



Alere Afinion™ AS100 Analyzer

The Alere Afinion AS100 Analyzer provides valuable near patient testing for today's healthcare professionals. The Alere Afinion Test System utilizes the latest technology and provides a simple, fast and reliable method by which to monitor patients' disease progression.

Simple. Fast. Reliable.

- Multi Assay Analyzer System
- 3 Minute HbA1c - CLIA Waived
- 5 Minute Albumin/Creatinine Ratio (ACR)
- Short test time provides the opportunity for more timely treatment changes
- Easy sample collection and operation, minimal training required
- Reliable, lab quality results



Alere Afinion AS100 Analyzer

Simple. Fast. Reliable.

3-step procedure



Facts

- 1.5 μ L sample volume.
- 4-15% HbA1c measuring range.
- 3 months Test Cartridge room temperature storage.
- Integrated sampling device.
- Ready to use liquid Controls in 2 levels.

Enhanced software features:

- Operator lockout, QC lockout, additional patient ID fields.

Connectivity

The Alere Afinion Data Connectivity Converter (ADCC) allows for simple transfer of patient and controls results from the Alere Afinion AS100 Analyzer to LIS/HIS system of choice.

- Results are transferred via Ethernet connection.
- Available standard formats of HL7 or ASTM (selectable by configuration).
- ADCC configuration is performed in a web interface that can be opened in a common web browser.



Alere Afinion Test Menu

Alere Afinion HbA1c	23046641
Alere Afinion ACR	23046642

In the United States:

For customer service, call 1-800-640-0640
To fax an order, use 1-800-290-0290
To order online: www.fisherhealthcare.com

