



Alere Afinion™ HbA1c

Test for quantitative determination of glycated Hemoglobin (HbA1c) in human whole blood, used to monitor metabolic control in patients with diabetes.

Simple. Fast. Reliable.

- 3 minutes test time
- Samples Types: Fingerstick, Venous samples collected in EDTA, Heparin, Citrate
- Excellent precision (< 3% CV)
- No interference from Hb variants
- NGSP and IFCC certified
- CLIA waived



3-step procedure



Facts

- 1.5 μ L sample volume.
- 4-15% HbA1c measuring range.
- 3 months Test Cartridge room temperature storage.
- Integrated sampling device.
- Ready to use liquid Controls in 2 levels.

Enhanced software features:

- Operator lockout, QC lockout, additional patient ID fields.

Connectivity

The Alere Afinion Data Connectivity Converter (ADCC) allows for simple transfer of patient and controls results from the Alere Afinion AS100 Analyzer to LIS/HIS system of choice.

- Results are transferred via Ethernet connection.
- Available standard formats of HL7 or ASTM (selectable by configuration).
- ADCC configuration is performed in a web interface that can be opened in a common web browser.



Alere Afinion Test Menu

Alere Afinion HbA1c	23046641
Alere Afinion ACR	23046642

In the United States:

For customer service, call 1-800-640-0640
To fax an order, use 1-800-290-0290
To order online: www.fisherhealthcare.com

