

Our "Pyrogen-Free" reagent reservoirs and tips are certified with an endotoxin level less than 0.06 EU/mL.

Unless endotoxins have no potential as a source of variability in your work, this specification is critical, and should be considered when choosing laboratory plasticware and tips.

Reagent Reservoirs & Reagent Coolers: Ideal pipetting companions.

We never cut corners, but when re-designing our reagent reservoirs, it was the right thing to do – along with a host of other improvements:

- Trimmed base corners and distinct pour-off spouts make it easy to empty reservoir without spills
- Unique deep well "trough within a trough" design allows even small amounts of liquid to be accessible to all pipette tips
- Sterile, pyrogen-free, RNase/DNase certified in bulk or individually wrapped packaging
- Well-marked graduated increments on the inside wall minimize reagent waste
- Optional lid available for 100mL units so reagents are protected from evaporation and dust
- Wide base and sturdy construction provides stability and avoids inadvertent spills
- Molded corner structures allow bulk packaged units to be easily separated for use
- Clearly marked for recycling



Here's an innovative way to keep your work from heating up – our reusable Reagent Cooler:

- Maintains reagents at <5°C for up to 2 hours
- Preserve integrity of reagents and extend working time with full reservoir cooling
- Custom fit for the 100mL reagent reservoir
- Non-toxic blue gel is encased in heavy-duty PVC, chills or freezes quickly, and can be used over and over

Ordering Information

VistaLab Reagent Reservoirs are available in a variety of volume sizes and packaging configurations.

Reservoir capacity

		25µL Reservoir capacity			
			21-381-27E Catalog number		
	RESERVOIR SIZE:	SMALL	SMALL	MEDIUM	LARGE
DESCRIPTIONS	Bulk, 100/case Pyrogen-free, RNase/DNase certified, sterile	25mL 21-381-27C	25mL Divided 21-381-27E	50mL 21-381-27G	100mL 21-381-27A
	Bulk, 200/case Pyrogen-free, RNase/DNase certified, sterile	25mL 21-385-102		50mL 321-385-104	100mL 21-385-100
	Bulk, 100/case non-sterile	25mL 22-145-101	25mL Divided 22-145-102	50mL 22-145-103	100mL 22-145-100
	Individually wrapped, 50/case Pyrogen-free, RNase/DNase certified, sterile	25mL 21-381-27D	25mL Divided 21-381-27F	50mL 21-381-27H	100mL 21-381-27B
	Individually wrapped, 100/case Pyrogen-free, RNase/DNase certified, sterile	25mL 21-385-103		50mL 21-385-105	100mL 21-385-101
	Individually wrapped with lid, 50/case Pyrogen-free, RNase/DNase certified, sterile				100mL 21-385-111
	Bulk, reservoir lid, 100/case Pyrogen-free, RNase/DNase certified, sterile				100mL 21-385-110
	Reservoir Cooler for 100mL reservoir				21-385-112



25mL Reagent Reservoir



25mL Divided Reagent Reservoir



50mL Reagent Reservoir



100mL Reagent Reservoir



100mL Reagent Reservoir with Lid





100mL Reagent Reservoir Cooler

Manufactured by



© 2015 Thermo Fisher Scientific Inc. All rights reserved. Trademarks used are owned as indicated at www.fishersci.com/trademarks.

In the United States:

For customer service, call 1-800-766-7000 To fax an order, use 1-800-926-1166 To order online: www.fishersci.com

In Canada:

For customer service, call 1-800-234-7437 To fax an order, use 1-800-463-2996 To order online: www.fishersci.ca